

TREE 8TX METAL - UNMANAGED SWITCH - 8 PORTS


8 port unmanaged switch
(UL-Listed)
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	19170106
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-8.0	19170106
ECLASS-9.0	19170402
ECLASS-10.1	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
ETIM-5.0	EC000734
customs tariff number	85176200
GTIN	4048879439466
Packaging unit	1
Electrical data Supply	
Operating voltage DC min.	9 V
Operating voltage DC max.	48 V
Industrial communication	
Data transmission rate max.	100 MBit/s
Industrial communication Ethernet functionality	
Auto-crossover	yes
Auto-negotiation	yes
duplex	Full duplex
Switch type	unmanaged

VLAN unmanaged (IEEE 802.1Q) yes

Diagnostics

Alarm contact no

Diagnostic No voltage

LED display Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529) IP50

Mechanical data | Material data

Color housing black

Material housing Metal

Mechanical data | Mounting data

Mounting method geschnappt

Suitable for mounting type Mounting rail TH35, (EN 60715)

Height 110 mm

Width 45,3 mm

Depth 89,6 mm

Environmental characteristics | Climatic

Operating temperature min. -10 °C

Operating temperature max. 70 °C

Storage temperature min. -40 °C

Storage temperature max. 85 °C

Connection type 2

Connection type 1	8
Connection type 2	X1
Family construction form	RJ45
Gender	female
Color contact carrier	black
No. of poles	8
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.
Connection	Plug-in terminals RK
Family construction form	terminal
Gender	male
Color contact carrier	green
No. of poles	5
PIN 1	24 V DC (UB 2)
PIN 2	0 V
PIN 3	24 V DC (UB 1)
PIN 4	0 V
PIN 5	PE