

**SIGNAL TOWER MODLIGHT30 EQUIPPED WITH LED MODULES**

Green,amber,red

Connection module + LED modules  
green, yellow, red  
Connection cable 3 m

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-8.0	27371230
ECLASS-9.0	27371230
ECLASS-10.1	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ETIM-5.0	EC001042
customs tariff number	85318070
GTIN	4048879311885
Packaging unit	1
Electrical data   Supply	
Operating voltage AC	24 V
Operating voltage DC	24 V
Current consumption max.	83 mA
Mechanical data   Material data	
Color housing	black
Material housing	Plastic
Mechanical data   Mounting data	
Height	30 mm

Width	30 mm
Depth	160 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-30 °C
Operating temperature max.	60 °C

**Connection type 1**

Family construction form	free cable end
No. of poles	6
PIN 1	Wire YE
PIN 2	LED WH
PIN 3	LED BU
PIN 4	LED GN
PIN 5	LED YE
PIN 6	LED RD