




PKB 2 FOR SIGNAL TRANSFER

250V / 25 A

4× 22-pole
25 A per potential rail
Screw plug-in terminals
Input terminal: max. 6 mm² single core, total current: max. 100 A

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27260708
ECLASS-7.0	27141152
ECLASS-8.0	27141152
ECLASS-9.0	27141152
ECLASS-10.1	27141152

ECLASS-11.1	27141152
ECLASS-12.0	27141152
ETIM-5.0	EC001283
customs tariff number	85369010
GTIN	4048879026055
Packaging unit	1

Electrical data | Supply

Operating voltage AC	250 V
Total current per potential rail max.	25 A

Installation

Connection cross-section solid max.	6 mm ²
Connection cross-section stranded/fine-stranded max.	4 mm ²
AWG number	9

Installation | Connection

Connection	Screw terminals SK
------------	--------------------

Device protection | Electrical

Overvoltage category (EN 60664-1)	II
-----------------------------------	----

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	75 mm
Width	135 mm
Depth	66 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C