

TREE 6TX ECO - UNMANAGED SWITCH - 6 PORTS

6 port unmanaged switch
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	19170106
ECLASS-7.0	19170106
ECLASS-8.0	19170106
ECLASS-9.0	19170106
ETIM-5.0	EC000734
customs tariff number	85176200
GTIN	4048879329569
Packaging unit	1
Electrical data Supply	
Operating voltage DC min.	9 V
Operating voltage DC max.	30 V
Industrial communication	
Data transmission rate max.	100 MBit/s
Industrial communication Ethernet functionality	
Auto-crossover	yes
Auto-negotiation	yes
duplex	Full duplex
Switch type	unmanaged
VLAN unmanaged (IEEE 802.1Q)	yes
Diagnostics	
Alarm contact	no
Diagnostic	No voltage

LED display

Ethernet connection/data traffic

Installation | Connection

Number ports 6

Device protection | Electrical

Degree of protection (EN IEC 60529) IP20

Mechanical data | Material data

Color housing black

Material housing Plastic

Mechanical data | Mounting data

Mounting method geschnappt

Suitable for mounting type Mounting rail TH35, (EN 60715)

Height 90 mm

Width 45,2 mm

Depth 78 mm

Environmental characteristics | Climatic

Operating temperature min. 0 °C

Operating temperature max. 60 °C

Storage temperature min. -10 °C

Storage temperature max. 70 °C