

LED-INDICATOR RED/GREEN

LED 5mm - 24V DC - 15mA - IP67

(red/green)  
24 V DC  
Protection IP67

[Link to Product](#)

Illustration



Product may differ from Image

| Commercial data       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27261590      |
| ECLASS-6.1            | 27261501      |
| ECLASS-7.0            | 27261501      |
| ECLASS-8.0            | 27261501      |
| ECLASS-9.0            | 27261501      |
| ECLASS-10.1           | 27261501      |
| ECLASS-11.1           | 27261501      |
| ECLASS-12.0           | 27261501      |
| ETIM-5.0              | EC000272      |
| customs tariff number | 85318070      |
| GTIN                  | 4048879040563 |

Packaging unit 10

**Electrical data | Supply**

|                           |        |
|---------------------------|--------|
| Operating voltage DC      | 24 V   |
| Operating voltage DC min. | 20,4 V |
| Operating voltage DC max. | 26,4 V |
| Current consumption min.  | 13 mA  |
| Current consumption max.  | 17 mA  |

**Installation | Connection**

Connection information Faston 2.8x0.8 mm

**Device protection | Electrical**

Degree of protection (EN IEC 60529) IP67

**Mechanical data**

Diameter LED 5 mm

**Mechanical data | Material data**

|                  |      |
|------------------|------|
| Color housing    | gray |
| Material housing | PVC  |

**Mechanical data | Mounting data**

|                               |         |
|-------------------------------|---------|
| Diameter front panel drilling | 8 mm    |
| Height                        | 18,5 mm |
| Width                         | 12 mm   |
| Depth                         | 53 mm   |

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -40 °C |
| Operating temperature max. | 70 °C  |