

MODLINK MSDD SOCKET INSERT USA NEMA 5-15

125VAC/15A screw connection

USA (NEMA 5-15)  
Screw terminals

Link to Product

Illustration



Product may differ from Image



Commercial data

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27189217      |
| ECLASS-6.1            | 27189217      |
| ECLASS-7.0            | 27189217      |
| ECLASS-8.0            | 27189217      |
| ECLASS-9.0            | 27182806      |
| ECLASS-10.1           | 27182806      |
| ECLASS-11.1           | 27182806      |
| ECLASS-12.0           | 27182806      |
| ETIM-5.0              | EC000020      |
| customs tariff number | 85366990      |
| GTIN                  | 4048879038263 |
| Packaging unit        | 1             |

Mechanical data | Mounting data

|        |       |
|--------|-------|
| Height | 88 mm |
| Width  | 51 mm |
| Depth  | 30 mm |

Environmental characteristics | Climatic

|                          |        |
|--------------------------|--------|
| Storage temperature min. | -10 °C |
| Storage temperature max. | 60 °C  |

USA

|                               |         |
|-------------------------------|---------|
| Connection cross section max. | 2,5 mm² |
| AWG number max.               | 14      |

|                            |                    |
|----------------------------|--------------------|
| Operating voltage AC       | 125 V              |
| Operating current          | 15 A               |
| Connection                 | Screw terminals SK |
| No. of poles               | 2 + PE             |
| Connections per pole       | 2                  |
| Protection contact present | yes                |