

**EOL - MODLIGHT70 CONNECTION MODULE**

Product discontinued

Basic + buzzer + flash (170 mm)

[Link to Product](#)**Illustration**

Product may differ from Image

**Technical Data**

Operating voltage	24 V DC (21.6...26.4 V DC)
Buzzer (infinitely adjustable)	Continuous and intermittent alarm
Sound pressure level	70 ±5...90 ±5 dB
Blink cycles	60 ±12 per minute

**General data**

Protection	IP65 inserted and tightened
Connection	Spring clamp terminals
Housing	Black plastic
Dimensions H×W×D	170×70×70 mm
Temperature range	-30...+60 °C

**Commercial data**

customs tariff number	85319000
GTIN	4048879030960
Packaging unit	1