

EOL - SIGNAL TOWER MODLIGHT50 EQUIPPED WITH LED MODULES

Product discontinued

Basic, buzzer, flash + LED modules  
green, yellow, red

Link to Product

Illustration



Product may differ from Image

Technical Data	
Operating voltage	24 V DC (21.6...26.4 V DC)
Current consumption	max. 62.5 mA
Sound pressure level	70 ±5...90 ±5 dB
Blink cycles	60 ±12 per minute
General data	
Protection	IP65 inserted and tightened
Connection	Spring clamp terminals
Housing	Black plastic
Dimensions H×W×D	293×50×50 mm
Temperature range	-30...+60 °C
Commercial data	
customs tariff number	85318070
GTIN	4048879322256
Packaging unit	1