

Mico Pro Power module

IN: 24 V DC / 40A, 16mm² / Cover plate included (heavy duty)

Mico Pro® PM 24 V DC/40 A
Cover plate included (heavy duty)
Shock load
1/2 sin 40 g, 11 ms
Build your own Mico Pro® online:
[START](#)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371802
ECLASS-6.1	27371890
ECLASS-7.0	27371890

ECLASS-8.0	27371890
ECLASS-9.0	27371802
ECLASS-10.1	27371802
ECLASS-11.1	27371802
ECLASS-12.0	27371802
ETIM-5.0	EC001440
customs tariff number	85363030
GTIN	4048879552080
Packaging unit	1

Electrical data | Supply

Total current max.	40 A
--------------------	------

Electrical data | Input

CTRL input voltage control inputs high min.	9 V
CTRL input voltage control inputs high max.	30 V
CTRL signal	ON/OFF
Input voltage 1 DC	12 V
Input voltage 2 DC	24 V
Input voltage DC min.	9 V
Input voltage DC max.	30 V
ON input voltage control inputs min.	9 V
ON input voltage control inputs max.	30 V
ON pulse length control inputs high min.	120 ms
Total current bridge set max.	40 A

Electrical data | Output

Switching voltage AC max.	30 V
Switching voltage DC max.	30 V

Installation

Connection cross-section static min.	0,75 mm ²
Connection cross section static max.	16 mm ²
Connection cross-section dynamic min.	0,75 mm ²
Connection cross section dynamic max.	16 mm ²
AWG number static min.	4
AWG number static max.	20
AWG number dynamic min.	4
AWG number dynamic max.	20

Installation | Connection

Connection	Bridge system
------------	---------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Device protection | Mechanical

Shock resistance (EN IEC 60068-2-27)	40 g, 11 ms 1/2 sin
--------------------------------------	---------------------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	130 mm
Width	24 mm
Depth	114 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	55 °C

Storage temperature min. -40 °C

Storage temperature max. 80 °C

Connection type 7

Family construction form Bridging Contact

Gender female

Color contact carrier black

No. of poles 1

PIN 1 UB In + 24 V DC

Family construction form Bridging Contact

Gender female

Color contact carrier black

No. of poles 1

PIN 1 0 V

Family construction form Bridging Contact

Gender female

Color contact carrier black

No. of poles 4

PIN 1 On

PIN 2 Ctrl

PIN 3 Alarm

PIN 4 0.9

Family construction form Bridging Contact

Gender male

Color contact carrier black

No. of poles 4

PIN 1 On

PIN 2 Ctrl

PIN 3 Alarm

PIN 4 0.9

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier green

No. of poles 2

PIN 1 13 Alarm

PIN 2 14 Alarm

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier green

No. of poles 2

PIN 1 23 90%

PIN 2 24 90%

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier green

No. of poles 2

PIN 1 Ctrl

PIN 2 On