

PROFIBUS-PLUG-MALE (SUB-D) 180°

Cut clamp for rigid and flexible wires

Art.No.: 55584
Weight: 0.033
Country of origin: DE
Model designation: Profibus Stecker 180°Schneidkl.

Bus connection plug 180°
PROFIBUS
SUB-D9 (male), IDC terminals, rigid and flexible cable, programming device connection
PROFIBUS, FC cable rigid/flexible, 1× 2× 0.64 mm², for outer diameter 8.0 ±0.5 mm

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC001855
customs tariff number	85389091
customs tariff number	85389091
GTIN	4048879050579
GTIN	4048879050579
Packaging unit	1
Packaging unit	1
Electrical data	
Terminating resistor	connectable, integrated
Electrical data Supply	

Operating voltage DC min.	4,75 V
---------------------------	--------

Operating voltage DC max.	5,25 V
---------------------------	--------

Current consumption max.	12,5 mA
--------------------------	---------

Industrial communication

Data transmission rate max.	12 MBit/s
-----------------------------	-----------

Installation | Connection

Connection	Cut clamps IDC
------------	----------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Pollution Degree	2
------------------	---

Mechanical data | Mounting data

Height	72 mm
--------	-------

Width	35 mm
-------	-------

Depth	17 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
----------------------------	--------

Operating temperature max.	85 °C
----------------------------	-------