

**MODLINK MSDD DATA INSERT**

2xUSB-A female/female + 2xRJ45

Art.No.: 4000-68000-0970000  
Weight: 0.077  
Country of origin: DE  
Model designation: Fr.Modul 2xRJ45 2xUSB Bf A gesch.

RJ45; RJ45; USB; USB (A)  
2× RJ45, 8-pole metal, CAT5e (female/female)  
2× USB (female/female) form A

**Link to Product**

**Illustration**



Product may differ from Image



| Commercial data                 |               |
|---------------------------------|---------------|
| ECLASS-6.0                      | 27189217      |
| ECLASS-6.1                      | 27189217      |
| ECLASS-7.0                      | 27189217      |
| ECLASS-8.0                      | 27189217      |
| ECLASS-9.0                      | 27182806      |
| ECLASS-10.1                     | 27182806      |
| ECLASS-11.1                     | 27182806      |
| ECLASS-12.0                     | 27182806      |
| ETIM-5.0                        | EC002625      |
| ETIM-6.0                        | EC002625      |
| ETIM-7.0                        | EC002625      |
| ETIM-8.0                        | EC002625      |
| customs tariff number           | 85366990      |
| customs tariff number           | 85366990      |
| EAN                             | 4048879037778 |
| EAN                             | 4048879037778 |
| Packaging unit                  | 1             |
| Packaging unit                  | 1             |
| Mechanical data   Mounting data |               |

|        |       |
|--------|-------|
| Height | 88 mm |
| Width  | 51 mm |
| Depth  | 60 mm |

#### Environmental characteristics | Climatic

|                          |        |
|--------------------------|--------|
| Storage temperature min. | -20 °C |
| Storage temperature max. | 60 °C  |

#### Shielding plate

|                        |                  |
|------------------------|------------------|
| Connection information | Threaded hole M4 |
| Tightening torque      | 0,9 Nm           |

#### USB

|                                  |                   |
|----------------------------------|-------------------|
| Operating voltage AC             | 48 V              |
| Operating voltage DC             | 48 V              |
| Operating voltage DC (UL-listed) | 42,4 V            |
| Operating current max.           | 500 mA            |
| USB specification                | 2.0               |
| Data transmission rate max.      | 480 MBit/s        |
| Looking techniques               | Snap-in connector |

#### RJ45

|                                       |                   |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | RJ45              |
| Family type Back side                 | RJ45              |
| Cable category min.                   | Cat5e             |
| Looking techniques                    | Snap-in connector |