

## MODLINK MSDD DATA INSERT

2×SUB-D9 female/female + 1×RJ45 + 1×USB-A

RJ45; USB (A); SUB-D9; SUB-D9  
 1× RJ45, 8-pole metal, CAT5e (female/female)  
 1× USB 2.0 (female/female) form A  
 2× SUB-D9 (female/female)

### Link to Product

#### Illustration



Product may differ from Image



#### Commercial data

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879037648
Packaging unit	1

#### Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	45 mm

#### Environmental characteristics | Climatic

Storage temperature min.	-30 °C
Storage temperature max.	60 °C

#### Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
<b>USB</b>	
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage DC (UL-listed)	42,4 V
Operating current max.	500 mA
USB specification	2.0
Data transmission rate max.	480 MBit/s
Looking techniques	Snap-in connector
<b>SUB-D9</b>	
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	3 A
Current operating max. (UL)	175 mA
Family construction form	SUB-D9
Family type Back side	SUB-D9
Gender	female
Gender Rear	female
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
No. of poles	9
<b>RJ45</b>	
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector