

**MODLINK MSDD DBL COMBI INSERT GREAT BRITAIN**

1xRJ45 fem./fem. + RCD opening

1× Great Britain (BS)

1× RJ45, 8-pole metal, CAT5e (female/female)

1× FI cut-out

**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27189217      |
| ECLASS-6.1              | 27189217      |
| ECLASS-7.0              | 27189217      |
| ECLASS-8.0              | 27189217      |
| ECLASS-9.0              | 27182806      |
| ECLASS-10.1             | 27182806      |
| ECLASS-11.1             | 27182806      |
| ECLASS-12.0             | 27182806      |
| ETIM-5.0                | EC000020      |
| GTIN                    | 4048879384506 |
| Gümrük tarife no (gtip) | 85366990      |
| Paket miktarı           | 1             |

**Mechanical data | Mounting data**

|        |        |
|--------|--------|
| Height | 88 mm  |
| Width  | 116 mm |
| Depth  | 70 mm  |

**Environmental characteristics | Climatic**

|                          |       |
|--------------------------|-------|
| Storage temperature min. | 5 °C  |
| Storage temperature max. | 40 °C |

**England**

|                      |       |
|----------------------|-------|
| Operating voltage AC | 250 V |
|----------------------|-------|

|                                       |                   |
|---------------------------------------|-------------------|
| Operating current                     | 13 A              |
| No. of poles                          | 2 + PE            |
| Protection contact present            | yes               |
| <b>RJ45</b>                           |                   |
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | RJ45              |
| Family type Back side                 | RJ45              |
| Cable category min.                   | Cat5e             |
| Looking techniques                    | Snap-in connector |