

**MODLINK MSDD SINGLE COMBI INSERT FRANCE**

1x RJ45 + 1x data cutout

1x France (UTE-NF) white

1x RJ45, 8-pole metal, CAT6A (female/female)

1x RJ45 cut-out

**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27189217      |
| ECLASS-6.1              | 27189217      |
| ECLASS-7.0              | 27189217      |
| ECLASS-8.0              | 27189217      |
| ECLASS-9.0              | 27182806      |
| ECLASS-10.1             | 27182806      |
| ECLASS-11.1             | 27182806      |
| ECLASS-12.0             | 27182806      |
| ETIM-5.0                | EC002625      |
| GTIN                    | 4048879601009 |
| Gümrük tarife no (gtip) | 85366990      |
| Paket miktarı           | 1             |

**Device protection | Electrical**

Degree of protection (EN IEC 60529) IP20

**Mechanical data | Mounting data**

|        |         |
|--------|---------|
| Height | 87,5 mm |
| Width  | 50,7 mm |
| Depth  | 43 mm   |

**Environmental characteristics | Climatic**

|                            |       |
|----------------------------|-------|
| Operating temperature min. | -5 °C |
| Operating temperature max. | 50 °C |

|                                       |                    |
|---------------------------------------|--------------------|
| Storage temperature min.              | -10 °C             |
| Storage temperature max.              | 60 °C              |
| <b>Shielding plate</b>                |                    |
| Connection information                | Threaded hole M4   |
| Tightening torque                     | 0,9 Nm             |
| <b>France (UTE-NF)</b>                |                    |
| Connection cross section max.         | 4 mm <sup>2</sup>  |
| AWG number max.                       | 12                 |
| Operating voltage AC                  | 250 V              |
| Operating current                     | 16 A               |
| Connection                            | Screw terminals SK |
| No. of poles                          | 2 + PE             |
| Connections per pole                  | 2                  |
| Protection contact present            | yes                |
| <b>RJ45</b>                           |                    |
| Operating voltage AC max. (UL-listed) | 30 V               |
| Operating voltage DC max. (UL-listed) | 42,4 V             |
| Current operating max. (UL)           | 175 mA             |
| Family construction form              | RJ45               |
| Family type Back side                 | RJ45               |
| Cable category min.                   | Cat6a              |
| Looking techniques                    | Snap-in connector  |