

**COMLIGHT56 LED BLUE STATUS LIGHT**

With 4 pole M12 bottom exit

Compact status light  
Flange M12 male, 4-pole  
blue

**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27371220      |
| ECLASS-6.1              | 27110390      |
| ECLASS-7.0              | 27110390      |
| ECLASS-8.0              | 27110390      |
| ECLASS-9.0              | 27110350      |
| ECLASS-10.1             | 27110350      |
| ECLASS-11.1             | 27110350      |
| ECLASS-12.0             | 27110350      |
| ETIM-5.0                | EC000232      |
| GTIN                    | 4048879855730 |
| Gümrük tarife no (gtip) | 85319000      |
| Paket miktarı           | 1             |

**Electrical data | Supply**

|                          |       |
|--------------------------|-------|
| Operating voltage DC     | 24 V  |
| Current consumption max. | 26 mA |

**Industrial communication | HMI**

|                    |         |
|--------------------|---------|
| Luminous intensity | 239 mcd |
|--------------------|---------|

**Device protection | Electrical**

|                                        |                  |
|----------------------------------------|------------------|
| Degree of protection (EN IEC 60529)    | IP65             |
| Additional condition protection degree | inserted, locked |

**Mechanical data | Material data**

|                  |         |
|------------------|---------|
| Material housing | Plastic |
|------------------|---------|

**Mechanical data | Mounting data**

|        |         |
|--------|---------|
| Height | 78,8 mm |
| Width  | 56 mm   |
| Depth  | 56 mm   |

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -30 °C |
| Operating temperature max. | 50 °C  |

**Connection type 1**

|                          |                  |
|--------------------------|------------------|
| Family construction form | M12              |
| Gender                   | male             |
| Coding                   | A                |
| No. of poles             | 4                |
| PIN 3                    | BU 0 V (24 V DC) |
| PIN 4                    | BK 24 V DC (0 V) |