

SVS VALVE PLUG FORM B 10 MM FIELD-WIREABLE




110V LED+VDR PG9

Form B (10 mm)
110 V AC/DC ±10%
LED and VDR
PG9

Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

Side 1	
Degree of protection (EN IEC 60529)	IP65
取引条件	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ETIM-5.0	EC002062
GTIN	4048879187282

HSコード	85366990
Packaging unit	1
Electrical data	
Capacity CX	10 ms
Holding power max.	100 W
Electrical data Supply	
Operating voltage AC	110 V
Operating voltage AC min.	99 V
Operating voltage AC max.	121 V
Operating voltage DC	110 V
Operating voltage DC min.	99 V
Operating voltage DC max.	121 V
Cut-off peak voltage max.	250 V
Current operating per contact max.	1 A
Current consumption max.	12 mA
Diagnostics	
Status indication LED	yellow
Installation	
Connection cross section max.	1,5 mm²
Installation Connection	
Tightening torque	0,4 Nm
Mounting set	M3
Device protection Electrical	
Additional condition protection degree	inserted, locked, with screw connection
Mechanical data Mounting data	
Mounting method	PG9
Clamping range min.	6 mm
Clamping range max.	8 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C