

MKDP 24/23 Cable entry plate

Product discontinued

Size 24

Cable diameter (23)× 4.1...8.1 mm

Ürün Linki

örnekleme



Ürün Image farklı olabilir

Ticari bilgiler

ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-8.0	27440102
ECLASS-9.0	27440116
ECLASS-10.1	27440106
ECLASS-11.1	27440106
ECLASS-12.0	27440116
ETIM-5.0	EC001855
GTIN	4048879568586
Gümrük tarife no (gtip)	39269097
Paket miktarı	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP66
-------------------------------------	------

Mechanical data | Material data

Combustibility class (UL94)	V-0
Material gasket	TPE
Material housing	PA

Mechanical data | Mounting data

Height	147,5 mm
Width	59,5 mm
Depth	25 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	100 °C