


Wall bushing for push pull power

With spring-cage connection, flexible coding

Push Pull Power metal mounting frame
incl. contact insert with spring clamp connection
flexible coding
Suitable for rectangular mounting cut-out
with gasket
without fixing screws

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27440210
ECLASS-11.1	27440210
ECLASS-12.0	27440210
ETIM-5.0	EC002635
Classificação fiscal	85366990
GTIN	4048879900454
Quantidade por embalagem	1
Electrical data Supply	
Operating voltage DC	24 V
Operating current	16 A
Installation	
Connection cross section min.	0,75 mm²
Connection cross section max.	2,5 mm²
AWG number min.	18

AWG number max. 13

Installation | Connection

Connection Spring clamp terminals FK

Mating cycles min. 100

Device protection | Electrical

Degree of protection (EN IEC 60529) IP65, IP67

Additional condition protection degree inserted, screwed

Pollution Degree 2

Rated surge voltage 4 kV

Mechanical data | Material data

Coating housing nickel plated

Combustibility class (UL94) V-0

Material housing Zinc die-casting

Mechanical data | Mounting data

Mounting method 5-pole, PPP

Environmental characteristics | Climatic

Operating temperature min. -40 °C

Operating temperature max. 70 °C