

8 mm crimp contact f/turned/silver/10 mm²

2 pieces

Turned crimp contact
Female
8 mm
10 mm² (AWG 8)
Quantity: 100 pcs.
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879649704
Packaging unit	2
Installation	
Connection cross section max.	10 mm²
AWG number max.	8
Installation Connection	
Stripping length	16 mm
Connection	Crimp
Gender	female
Mating cycles min.	500
Mechanical data Material data	
Coating contact	silver-plated

Brass

Height	13 mm
Width	13 mm
Depth	43 mm

Depth	43 mm
-------	-------