

### Mini (7/8) 3 pole, Male (Ext.) Straight/Female Straight,

TPE, TC-ER+FT4, 3x16AWG, yellow, 7.5m

Male straight – female straight

7/8" – 7/8", 3-pole

Power cable

USA





Further cable lengths on request.


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

#### Illustration





Product may differ from Image



|                                        |                   |
|----------------------------------------|-------------------|
| Cable length                           | 7,5 m             |
| Side 1                                 |                   |
| Tightening torque                      | 1,5 Nm            |
| Family construction form               | 7/8"              |
| Thread                                 | 7/8"              |
| Width across flats                     | SW24              |
| Side 2                                 |                   |
| Tightening torque                      | 1,5 Nm            |
| Thread                                 | 7/8"              |
| 取引条件                                   |                   |
| ECLASS-6.0                             | 27279218          |
| ECLASS-7.0                             | 27279218          |
| ECLASS-8.0                             | 27279218          |
| ECLASS-9.0                             | 27060311          |
| ECLASS-10.1                            | 27060311          |
| ECLASS-11.1                            | 27060311          |
| ECLASS-12.0                            | 27060327          |
| ETIM-5.0                               | EC001855          |
| GTIN                                   | 4048879632928     |
| HSコード                                  | 85444290          |
| Packaging unit                         | 1                 |
| Electrical data   Supply               |                   |
| Operating voltage AC max.              | 600 V             |
| Operating voltage DC max.              | 600 V             |
| Current operating per contact max.     | 12 A              |
| Device protection   Electrical         |                   |
| Degree of protection (EN IEC 60529)    | IP68              |
| Additional condition protection degree | inserted, screwed |
| Mechanical data   Material data        |                   |
| Coating locking                        | Nickeled          |
| Material housing                       | PUR               |

