

**POWER DISTRIBUTOR PD4 PLUG 24+E**

Connector for 27680 and 27681

Industry female plug 24+PE  
Field-wireable

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27279219
ECLASS-6.1	27142601
ECLASS-7.0	27142601
ECLASS-8.0	27142601
ECLASS-9.0	27142601
ECLASS-10.1	27142601
ECLASS-11.1	27142606
ECLASS-12.0	27142606
ETIM-5.0	EC002585
customs tariff number	85366990
GTIN	4048879063432
Packaging unit	1
Electrical data	
Security level	SELV
Electrical data   Supply	
Operating voltage AC	50 V
Operating voltage DC	120 V
Current operating per contact max.	9 A
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed

**Mechanical data | Material data**

Coating housing	powder-coated
Material housing	Aluminum die casting

**Mechanical data | Mounting data**

Clamping range min.	9 mm
Clamping range max.	17 mm
Height	120 mm
Width	43 mm
Depth	70 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-30 °C
Operating temperature max.	85 °C