

POTENTIAL TERMINAL BLOCK BLUE YELLOW

Potential terminal block
blue/yellow

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27141106
ECLASS-6.1	27141106
ECLASS-7.0	27141106
ECLASS-8.0	27141106
ECLASS-9.0	27141106
ECLASS-10.1	27141106
ECLASS-11.1	27141106
ECLASS-12.0	27141106
ETIM-5.0	EC001283
customs tariff number	85369010
GTIN	4048879049368
Packaging unit	1
Electrical data Supply	
Operating voltage AC max.	30 V
Operating voltage DC max.	30 V
Total current max.	10 A
Installation	
Connection cross section max.	2,5 mm²
AWG number min.	28
AWG number max.	14
Installation Connection	
Connection	Spring clamp plug-in terminals
Device protection Electrical	

Degree of protection (EN IEC 60529) IP20

Mechanical data | Mounting data

Height	70 mm
Width	56 mm
Depth	32,5 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C