

CUBE20S POWER MODULE

24VDC + 5VDC/2A

Power module
Expansion module
for external voltage supply and internal backplane

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27242610
ECLASS-6.1	27242611
ECLASS-7.0	27242611
ECLASS-8.0	27242611
ECLASS-9.0	27242611
ECLASS-10.1	27242611
ECLASS-11.1	27242611
ECLASS-12.0	27242611
ETIM-5.0	EC001600
customs tariff number	85369010
GTIN	4048879422895
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Total current max.	6 A
Electrical data Input	
Input voltage DC	24 V
Input voltage DC min.	20,4 V
Input voltage DC max.	28,8 V
Electrical data Output	

Output voltage DC	24 V
-------------------	------

Output current	4 A
----------------	-----

Current output backplane bus max.	2 A
-----------------------------------	-----

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Mounting method	geschnappt
-----------------	------------

Suitable for mounting type	mounting rail, (EN 60715)
----------------------------	---------------------------

Height	109 mm
--------	--------

Width	12,9 mm
-------	---------

Depth	76,5 mm
-------	---------

Environmental characteristics | Climatic

Operating temperature min.	0 °C
----------------------------	------

Operating temperature max.	60 °C
----------------------------	-------

Storage temperature min.	-25 °C
--------------------------	--------

Storage temperature max.	70 °C
--------------------------	-------

Connection type 1

Connection type 1	Power
-------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

No. of poles	8
--------------	---

PIN 1	n.c.
-------	------

PIN 2	24 V DC
-------	---------

PIN 3	0 V
-------	-----

PIN 4	24 V DC Sys
-------	-------------

PIN 5	n.c.
-------	------

PIN 6	24 V DC
-------	---------

PIN 7	0 V
-------	-----

PIN 8	0 V Sys
-------	---------