

Xenterra 5TX GE  
 5 port unmanaged switch  
 DIN-rail mountable TH35 (EN 60715)  
 Connection cables are in the online shop under "Connection Technology".

## Link to Product

### Illustration



Product may differ from Image

### Approvals



### More Info

Bus technologies

### General data

Mounting method	DIN-rail mountable TH35 (EN 60715)
Temperature range	-40...+70 °C (storage temperature -40...+85 °C)
Housing	Metal black
Protection	IP20
Dimensions HxWxD	105x110x37.8 mm

### Technical Data

Operating voltage	8...28 V AC/9...36 V DC
Transfer rate	10/100/1000 Mbit/s full duplex
Operating modes	Autocrossing Autonegotiation

### Connections

Fieldbus	5x RJ45
Supply	Push-In spring clamp terminals, 0.2...2.5 mm <sup>2</sup> (0.25...1.5 mm <sup>2</sup> )

### Switch Management

Protocols	no
Port Mirroring	no
VLAN (QoS) IEEE 802.p	yes
Alarm contact	no
Remote maintenance	no
Webserver	no

Switch Form Unmanaged Switch

**Diagnostic**

Communication status via LED

Monitoring - no voltage yes

**Commercial data**

country of origin DE

customs tariff number 85176200

EAN 4048879830447

Packaging unit 1.000