


MDD DC/DC-CONVERTOR SWITCH MODE

IN: 24VDC OUT: 2x15V/0,25ADC

INPUT: 24 V DC
OUTPUT: ± 15 V DC
Output rating: 7 W
Current: 2×0.25 A
Condensation not permitted
Restart after overload by removing supply voltage

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27210901
ECLASS-6.1	27210901
ECLASS-7.0	27210901
ECLASS-8.0	27210901

ECLASS-9.0	27210901
ECLASS-10.1	27210901
ECLASS-11.1	27210901
ECLASS-12.0	27210901
ETIM-5.0	EC002540
customs tariff number	85043121
GTIN	4048879079518
Packaging unit	1

Electrical data

Security level	SELV
----------------	------

Electrical data | Input

Fuse protection primary side internal	1,5 A
Characteristic back-up fuse	Inertia
Input voltage DC	24 V
Current input AC	0,85 A

Electrical data | Output

Output voltage DC	15 V
Output voltage DC min.	14,25 V
Output voltage DC max.	15,75 V
Output voltage adjustable	no
Output current per channel max.	0,25 A
Ripple max.	0,2 %

Device protection | Electrical

Overload resistant	yes
Short-circuit protected	yes
Insulation test voltage input - output	4 kV

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	50 °C

Conformity

Low Voltage Directive	EN 61204-3
-----------------------	------------