



MIRO 6.2 PLUGGABLE COMPL.MODULE OUTPUT RELAY

IN: 230 VAC/DC - OUT: 250 VAC/30VDC / 6 A

- 1 NO/NC contact
- 230 V AC/DC
- Spring clamp terminals

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371601
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-8.0	27371601
ECLASS-9.0	27371601
ECLASS-10.1	27371601

ECLASS-11.1	27371601
ECLASS-12.0	27371601
ETIM-5.0	EC001437
customs tariff number	85364900
GTIN	4048879021418
Packaging unit	1
Electrical data Input	
Input voltage AC	230 V
Input voltage AC min.	184 V
Input voltage AC max.	264 V
Input voltage DC	230 V
Input voltage DC min.	184 V
Input voltage DC max.	264 V
Input current	4 mA
Electrical data Output	
Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24, 6 A @ 110 V, 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V, 3 A @ 110 V, 1,5 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V, 0,2 A @ 110 V, 0,1 A @ 230 V
Switching frequency max.	10 Hz
Power rating AC max.	1500 VA
Power rating DC max.	180 W
Switching voltage AC max.	250 V
Switching voltage DC max.	30 V
Switching current DC	100 mA
Switching current max.	6 A
Diagnostics	
Status indication LED	green
Device protection	
Condition lifetime	load-dependent
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Rated insulation voltage	250 V
Electrical lifetime NC	10000 Cycles
Electrical lifetime NO	30000 Cycles
Device protection Mechanical	
Mechanical endurance	10000000 Cycles
Mechanical data	
Drop-out time max.	4 ms
Response time max.	8 ms
Mechanical data Material data	
Material contact	Ag Sn O2
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	93 mm
Width	6,2 mm
Depth	75,6 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C

Connection type 5

Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	12
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	11
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	14
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	A 1
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	A 2