




**M12 female 0° B-cod. screw terminal shielded**

2-pol., max. 0.75mm², 6 - 8mm, shielded

Female straight  
M12, 2-pole  
B-coded  
shielded  
Screw terminals  
Sealing range (cable Ø): 6...8 mm

[Link to Product](#)

Illustration



Product may differ from Image

Side 1	
Family construction form	M12
Degree of protection (EN IEC 60529)	IP67
Commercial data	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27440102

ECLASS-11.1	27440102
ECLASS-12.0	27440116
ETIM-5.0	EC002635
customs tariff number	85366990
GTIN	4048879198615
Packaging unit	1
<b>Electrical data   Supply</b>	
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
<b>Installation</b>	
Connection cross section max.	0,75 mm²
<b>Device protection   Electrical</b>	
Additional condition protection degree	inserted, screwed
<b>Mechanical data   Material data</b>	
Coating housing	nickel plated
Material housing	Brass
<b>Mechanical data   Mounting data</b>	
Clamping range min.	6 mm
Clamping range max.	8 mm
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C