

MODL. VARIO 4-way fixed housing type B

nickel plated aluminum

Stationary housing (round)
4-way
Aluminium
Screw locking
Good chemical and oil resistance (oil resistance does not apply to use with PVC cable)
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

Commercial data

ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
customs tariff number	85389099
GTIN	4048879572965
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed

Mechanical data

Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar

Mechanical data | Material data

Coating housing	powder-coated
Material housing	Aluminum die casting

Mechanical data | Mounting data

Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	120 °C