

MODL. VARIO 8-way fixed housing type B

stainless steel type 1.4404 (V4A)

Stationary housing  
Stainless steel 1.4404 (V4A)  
8-way

Link to Product

Illustration



Product may differ from Image

Commercial data

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27260702      |
| ECLASS-6.1            | 27260708      |
| ECLASS-7.0            | 27440312      |
| ECLASS-8.0            | 27440312      |
| ECLASS-9.0            | 27440312      |
| ECLASS-10.1           | 27440312      |
| ECLASS-11.1           | 27440312      |
| ECLASS-12.0           | 27440312      |
| ETIM-5.0              | EC002641      |
| customs tariff number | 85389099      |
| GTIN                  | 4048879573146 |
| Packaging unit        | 1             |

Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP65, IP67, IP68  |
| Degree of protection (ISO 20653:2013)  | IP66K, IP69K      |
| Additional condition protection degree | inserted, screwed |

Mechanical data | Material data

|                  |                              |
|------------------|------------------------------|
| Material housing | Stainless steel 1.4404 (V4A) |
|------------------|------------------------------|

Mechanical data | Mounting data

|                 |              |
|-----------------|--------------|
| Mounting method | screw fixing |
|-----------------|--------------|

Environmental characteristics | Climatic

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -20 °C |
| Operating temperature max. | 120 °C |