

MODL. VARIO 10-way coupling housing type B

stainless steel type 1.4404 (V4A)

Mobile housing  
Stainless steel 1.4404 (V4A)  
10-way

Link to Product

Illustration



Product may differ from Image

| Commercial data                          |                              |
|------------------------------------------|------------------------------|
| ECLASS-6.0                               | 27260702                     |
| ECLASS-6.1                               | 27260708                     |
| ECLASS-7.0                               | 27440312                     |
| ECLASS-8.0                               | 27440312                     |
| ECLASS-9.0                               | 27440312                     |
| ECLASS-10.1                              | 27440312                     |
| ECLASS-11.1                              | 27440312                     |
| ECLASS-12.0                              | 27440312                     |
| ETIM-5.0                                 | EC002641                     |
| customs tariff number                    | 85389099                     |
| GTIN                                     | 4048879573177                |
| Packaging unit                           | 1                            |
| Device protection   Electrical           |                              |
| Degree of protection (EN IEC 60529)      | IP65, IP67, IP68             |
| Degree of protection (ISO 20653:2013)    | IP66K, IP69K                 |
| Additional condition protection degree   | inserted, screwed            |
| Mechanical data                          |                              |
| Operating pressure min.                  | -0,8 bar                     |
| Operating pressure max.                  | 16 bar                       |
| Mechanical data   Material data          |                              |
| Material housing                         | Stainless steel 1.4404 (V4A) |
| Mechanical data   Mounting data          |                              |
| Mounting method                          | screw fixing                 |
| Environmental characteristics   Climatic |                              |
| Operating temperature min.               | -20 °C                       |

Operating temperature max. 120 °C