

MODL. VARIO 8-way rectangle fixed housing

nickel plated aluminum, varnished aluminium

Stationary housing (rectangular)  
8-way

Link to Product

Illustration



Product may differ from Image

| Commercial data                          |                      |
|------------------------------------------|----------------------|
| ECLASS-6.0                               | 27260702             |
| ECLASS-6.1                               | 27260708             |
| ECLASS-7.0                               | 27440312             |
| ECLASS-8.0                               | 27440312             |
| ECLASS-9.0                               | 27440312             |
| ECLASS-10.1                              | 27440312             |
| ECLASS-11.1                              | 27440312             |
| ECLASS-12.0                              | 27440312             |
| ETIM-5.0                                 | EC002641             |
| customs tariff number                    | 85389099             |
| GTIN                                     | 4048879621823        |
| Packaging unit                           | 1                    |
| Device protection   Electrical           |                      |
| Degree of protection (EN IEC 60529)      | IP65, IP67, IP68     |
| Degree of protection (ISO 20653:2013)    | IP66K, IP69K         |
| Additional condition protection degree   | inserted, screwed    |
| Mechanical data   Material data          |                      |
| Coating housing                          | powder-coated        |
| Material housing                         | Aluminum die casting |
| Mechanical data   Mounting data          |                      |
| Looking techniques                       | Clip locking         |
| Environmental characteristics   Climatic |                      |
| Operating temperature min.               | -20 °C               |
| Operating temperature max.               | 120 °C               |