

MODL.VARIO Accessories closure plug 8/6

for adaptive inserts, nickel plated brass

Modlink Vario  
Accessories  
Locking plug  
Diameter  
8 mm  
Quantity: 10 pcs.  
good resistance to oil, gasoline and chemicals  
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27260702
ECLASS-6.1	27269202
ECLASS-7.0	27449203
ECLASS-8.0	27449203
ECLASS-9.0	27440192
ECLASS-10.1	27440192
ECLASS-11.1	27440192
ECLASS-12.0	27440192
ETIM-5.0	EC002641
customs tariff number	85389099
GTIN	4048879618892
Packaging unit	10
Mechanical data	
Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar
Mechanical data   Material data	
Coating housing	nickel plated
Material housing	Brass
Mechanical data   Mounting data	
Size	AD8
Height	19 mm

Width	10 mm
Depth	10 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
Operating temperature max.	120 °C