SUPPRESSOR FOR CONTACTORS

RC, 230 VAC/DC, 15 VA/W

Art.No.: 20002
Weight: 0.018 kg
Country of origin: CZ
Model designation: RC-A0 O22/230

230 V AC/DC
RC
For other configurations and voltages, please inquire.

Link to Product

Illustration





Product may differ from Image

Commercial data

URL Webshop	https://shop.murrelektronik.com/20002
GTIN	4048879020732
EU-Customs tariff number	85363010
US-Customs tariff number	8536308000

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-10

ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-7.1	27371013
ECLASS-8.0	27371013
ECLASS-8.1	27371013
ECLASS-9.0	27371013
ECLASS-9.1	27371013
ECLASS-10.0.1	27371013
ECLASS-10.1	27371013
ECLASS-11.0	27371013
ECLASS-11.1	27371013
ECLASS-12.0	27371013
ECLASS-13.0	27371013
ECLASS-14.0	27371013
ETIM-5.0	EC002498
ETIM-6.0	EC002498
ETIM-7.0	EC002498
ETIM-8.0	EC002498
ETIM-9.0	EC002498
ETIM-10.0	EC002498
customs tariff number	85363010
EAN	4048879020732
Packaging unit	1
Electrical data	
Damping factor	1.5× UN
Holding power max.	15 W
Electrical data | Input	
Input voltage AC min.	110 V
Input voltage AC max.	250 V
Input voltage DC min.	110 V
Input voltage DC max.	250 V
Installation | Connection	
Connection information	self-securing cable forks
Device protection | Media	
Flame resistance	flame retardant
Mechanical data | Material data	
housing	Plastic
Combustibility class housing (UL94)	V-0
Mechanical data | Mounting data	
Height	30 mm
Width	20 mm
Depth	13 mm
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	70 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-10