## MOTOR SUPPRESSOR

RC, 3x690VAC/7,5kW

Art.No.: 23104
Weight: 0.160 kg
Country of origin: CZ
Model designation: RC 3 BUG/690-7,5

3× 400 V AC
3× 575 V AC
3× 690 V AC
RC
For DIN-rail mounting use 2×Art.-No. 20900 adapter feet
Suppressors for other voltages, frequencies, and motor ratings available on request. Do not use RC motor suppressors with frequency inverters.

**Link to Product**

### Illustration







Product may differ from Image

### Commercial data

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-10-16

| | |
|---|---|
| URL Webshop | https://shop.murrelektronik.com/23104 |
| GTIN | 4048879019347 |
| EU-Customs tariff number | 85363010 |
| US-Customs tariff number | 8536308000 |
| ECLASS-6.0 | 27371013 |
| ECLASS-6.1 | 27371013 |
| ECLASS-7.0 | 27371013 |
| ECLASS-7.1 | 27371013 |
| ECLASS-8.0 | 27371013 |
| ECLASS-8.1 | 27371013 |
| ECLASS-9.0 | 27371013 |
| ECLASS-9.1 | 27371013 |
| ECLASS-10.0.1 | 27371013 |
| ECLASS-10.1 | 27371013 |
| ECLASS-11.0 | 27371013 |
| ECLASS-11.1 | 27371013 |
| ECLASS-12.0 | 27371013 |
| ECLASS-13.0 | 27371013 |
| ECLASS-14.0 | 27371013 |
| ETIM-5.0 | EC000683 |
| ETIM-6.0 | EC000683 |
| ETIM-7.0 | EC000683 |
| ETIM-8.0 | EC000683 |
| ETIM-9.0 | EC000683 |
| ETIM-10.0 | EC000683 |
| customs tariff number | 85363010 |
| EAN | 4048879019347 |
| Packaging unit | 1 |
| **Electrical data \| Supply** | |
| Power frequency | 50 ... 60 Hz |
| **Electrical data \| Input** | |
| Input voltage AC | 690 V |
| **Installation** | |
| Connection cross section max. | 1 mm² |
| **Installation \| Connection** | |
| Length single strands | 500 mm |
| Connection information | Single strands |
| **Device protection \| Media** | |
| Flame resistance | flame retardant |
| **Mechanical data \| Material data** | |
| housing | Plastic |
| Combustibility class housing (UL94) | V-0 |
| Material potting compound | 2-component epoxy |
| **Mechanical data \| Mounting data** | |
| Height | 92 mm |
| Width | 61 mm |
| Depth | 25 mm |
| Mounting method | geschnappt |
| Suitable for mounting type | Mounting rail TH35, (EN 60715) |
| **Environmental characteristics \| Climatic** | |
| Operating temperature min. | -20 °C |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-10-16

| | |
|---|---|
| Operating temperature max. | 60 °C |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-10-16