

MPU UW ANALOG COUPLER COMPONENT



IN: 0..10 V - OUT: 0..10 V / 300 mA

INPUT: 0...10 V DC
OUTPUT: 0...10 V DC, 300 mA
Screw terminals


This product is a processing component and must only be used by authorized manufacturers or people.
Input and output galvanically separated

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27210990
ECLASS-6.1	27210901
ECLASS-7.0	27210901
ECLASS-8.0	27210901
ECLASS-9.0	27210901

ECLASS-10.1	27210901
ECLASS-11.1	27210901
ECLASS-12.0	27210901
ETIM-5.0	EC002477
customs tariff number	85437090
GTIN	4048879028516
Packaging unit	1

Electrical data

Accuracy (of full scale)	0,5 %
--------------------------	-------

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	19,2 V
Operating voltage DC max.	28,8 V
Operating current max.	300 mA

Electrical data | Input

Input resistor	10 kΩ
----------------	-------

Electrical data | Output

Output current max.	0,3 A
---------------------	-------

Industrial communication

Transmission frequency max.	1000 Hz
-----------------------------	---------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	62 mm
Width	43 mm
Depth	67,5 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	50 °C

Connection type 2

Connection type 1	Input / Output
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	5
PIN 1	+
PIN 2	+
PIN 3	-
PIN 4	-
PIN 5	In
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	5
PIN 1	+
PIN 2	+
PIN 3	-
PIN 4	-
PIN 5	Out