





**MIRO 6.2 24V-1U OUTPUT REL. WITH ISOLATION FUNCT.**

IN: 24 VAC/DC - OUT: 250 VAC/DC / 6 A

1 NO/NC contact  
6 A  
24 V AC/DC  
with output isolation link  
Screw terminals

[Link to Product](#)**Illustration**



Product may differ from Image

### Approvals



### General data

Mech./ elect. life	20 000 000 switching cycles/load dependent
Test isolation voltage	4 kV; safe separation (EN 60947-1)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	-20...+55 °C
Dimensions H×W×D	91×6.2×70 mm

### Output

Switching voltage	max. 250 V AC/DC
Switching current per output	max. 6 A
Min. load current	100 mA (12 V DC)
Power rating (voltage dependent)	max. 1500 VA/120 W
Switching frequency	max. 10 Hz
Contact material	Ag Sn O <sub>2</sub>
Energize/release/contact bounce time	10/15/1.5 ms

### Input

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 03/21

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Connection voltage - current	24 V AC/DC (19.2...30 V AC/DC) - 17 mA
LED display	LED (green)
<b>Utilization category</b>	
AC-12	6 A (24/110/230 V AC)
AC-15	3 A (24/110/230 V AC)
DC-13	1 A (24 V DC); 0.2 A (110 V DC); 0.1 A (230 V DC)
<b>Commercial data</b>	
country of origin	CZ
customs tariff number	85364900
EAN	4048879027236
eClass	27371001
Packaging unit	1