


MASI20 INSTALLATION TECHNOLOGY

Distributor AS-I and extern power, 3 potentials

- 5 ports, universal
- 3 potentials
- 5 plug terminals included

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-8.0	27279219
ECLASS-9.0	27440108
ECLASS-10.1	27440111

ECLASS-11.1	27440111
ECLASS-12.0	27440111
ETIM-5.0	EC001596
customs tariff number	85366990
GTIN	4048879050500
Packaging unit	1
<b>Electrical data   Supply</b>	
Operating voltage DC max.	36 V
Current operating per port max.	8 A
Total current max.	12 A
<b>Device protection   Electrical</b>	
Degree of protection (EN IEC 60529)	IP20
Insulation strength Power/Power (EN 60664-1)	50 V
Insulation strength ASI/Power	200 V
<b>Mechanical data   Mounting data</b>	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	25 mm
Width	61 mm
Depth	152 mm
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-20 °C
Operating temperature max.	70 °C
<b>Conformity</b>	
Product standard	EN 60664-1
<b>Connection type 6</b>	
Connection type 1	11
Connection type 2	12
Connection type 3	13
Connection type 4	21
Connection type 5	31
Connection type 6	123
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	1 +
PIN 2	11 -
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	12 +
PIN 2	12 -
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2

PIN 1	13 +
PIN 2	13 -
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	21 +
PIN 2	21 -
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	31 +
PIN 2	31 -
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	6
PIN 1	11 +
PIN 2	1 -
PIN 3	2 +
PIN 4	2 -
PIN 5	3 +
PIN 6	3 -