

MA5I68 I/O EXTENSION MODULE

8 digital inputs

Expansion module
DI8 - 0.19 A (E) - 4× M12 (AB) AUX
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
customs tariff number	85176200
GTIN	4048879332484
Packaging unit	1
Electrical data Supply	
Bus voltage AS-Interface DC min.	26,5 V
Bus voltage AS-Interface DC max.	31,6 V
Current consumption AS-i port max.	250 mA
Electrical data Input	
Overload resistant	yes
Short-circuit protected	yes
Type input	PNP, for 3-wire sensors or mechanical switches

Current carrying capacity max. 0,19 A

Industrial communication | Bus data

Address setting type M12 connection and programming device, Master
 Slave address range (0), 1 A...31 A, 1 B...31 B

Industrial communication | AS-Interface

Profile (IO.ID.ID2) 2× S-0.A.2

Diagnostics

Diagnostic No voltage
 Diagnostic via LED per module
 LED display Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529) IP68

Mechanical data | Mounting data

Mounting method screwed
 Height 151 mm
 Width 30 mm
 Depth 34,5 mm

Environmental characteristics | Climatic

Operating temperature min. -20 °C
 Operating temperature max. 60 °C
 Storage temperature min. -20 °C
 Storage temperature max. 70 °C

Connection type 3

Connection type 1 A-D
 Connection type 2 Bus In
 Connection type 3 Bus Out
 Family construction form M12
 Gender female
 Color contact carrier black
 Coding A
 No. of poles 5
 PIN 1 Usens +
 PIN 2 DI
 PIN 3 Usens -
 PIN 4 DI
 PIN 5 n.c.
 Family construction form M12
 Gender male
 Color contact carrier black
 Coding A
 No. of poles 4
 PIN 1 AS-i +
 PIN 2 0 V
 PIN 3 AS-i -
 PIN 4 24 V DC
 Family construction form M12
 Gender male
 Color contact carrier black
 Coding A
 No. of poles 5
 PIN 1 AS-i +

PIN 2	0 V
PIN 3	AS-i -
PIN 4	24 V DC
PIN 5	n.c.