

CUBE67 ACCESSORIES

System interface connector

M12
Female straight
Internal system connection

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27242692
ECLASS-6.1	27242692
ECLASS-7.0	27242692
ECLASS-8.0	27242692
ECLASS-9.0	27242692
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC001583
customs tariff number	85366990
GTIN	4048879047883
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Operating current max.	4 A
Installation Connection	
Connection information	Han-Brid®, 6-polig
Family construction form	M12
Gender	female
Mating cycles min.	500
Installation Pin assignment	
No. of poles	6
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Mechanical data Mounting data	

Height	80,5 mm
--------	---------

Width	34 mm
-------	-------

Depth	32 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max.	85 °C
----------------------------	-------