

## 10 Port unmanaged Gigabit Switch 4 PoE 2 SFP Ports IP20 metal

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Approvals



#### More Info

#### Bus technologies

#### General data

Mounting method	DIN-rail mountable TH35 (EN 60715)
Temperature range	-40...+70 °C (storage temperature -40...+85 °C)
Housing	Metal black
Protection	IP20
Dimensions HxWxD	145x57.8x113 mm

#### Technical Data

Operating voltage	12...57 V DC
Transfer rate	10/100/1000 Mbit/s full duplex
Operating modes	Autocrossing Autonegotiation

#### Connections

Fieldbus	6x RJ45; 2x SFP
Supply	Screw terminals

#### Switch Management

Protocols	no
Port Mirroring	no
VLAN (QoS) IEEE 802.p	no
Alarm contact	yes
Remote maintenance	no
Websserver	no

