



ASSEMBLY MODULE MP 12

Mounting rail / screw-type terminal

12 pairs of solder pins
screw terminals connected to solder pin pairs

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27260710
ECLASS-6.1	27141149
ECLASS-7.0	27141149
ECLASS-8.0	27141149
ECLASS-9.0	27141149
ECLASS-10.1	27141149
ECLASS-11.1	27141149
ECLASS-12.0	27141149

ETIM-5.0	EC002780
customs tariff number	85369010
GTIN	4048879042253
Packaging unit	1
Electrical data Supply	
Operating voltage AC	50 V
Operating voltage DC	50 V
Operating current max.	5 A
Installation	
Connection cross section max.	4 mm ²
Installation Connection	
Connection	Screw terminals SK
Connection information	Lötstützpunktpaare (Raster 5 mm)
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Housing properties	open design
Material housing	Plastic
Mechanical data Mounting data	
Distance of solder pins	24 mm
Mounting method	screwed, geschnappt
Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)
Height	63 mm
Width	70 mm
Depth	36 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C