

**LED - LT 24/GREEN**

(green)  
24 V DC  
with lamp test input  
The modules are suitable for wall thickness of 1.5...5.0 mm.

[Link to Product](#)**Illustration**

Product may differ from Image

**General data**

Housing	Plastic, flame retardant
LED Ø	5 mm
Front panel hole diameter Ø	9 mm
Connection	Faston 2.8x0.8 mm
Temperature range	-20...+50 °C

**Technical Data**

Operating voltage	24 V DC ±15%
Current consumption	10 mA
Protection (IEC 60529/EN 60529)	IP65

**Commercial data**

country of origin	CZ
customs tariff number	85318070
EAN	4048879041225
eClass	27261590
Packaging unit	10