



IN: 230/400+/-15VAC OUT: 24V/2,5ADC

Condensation not permitted

Illustration



ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701
ECLASS-10.1	27040701

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
customs tariff number	85044095
GTIN	4048879080071
Packaging unit	1

Electrical data

Security level	SELV
----------------	------

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Fuse protection 1 primary side external	0,8 A @230 V AC
Fuse protection 2 primary side external	5 A @400 V AC
Characteristic back-up fuse	Inertia
Input voltage 1 AC	230 V
Input voltage 2 AC	400 V
Input current at input voltage 1 AC	0,5 A
Input current at input voltage 2 AC	0,28 A

Electrical data | Output

Fuse protection secondary side external	7,5 A
Output suppression	LED, Screening capacitor, VDR
Output voltage DC	24 V
Output voltage adjustable	no
Output current max.	3 A
Type of secondary fuse	Flat fuse FKS
Ripple max.	5 %

Mechanical data | Mounting data

Suitable for mounting type	Schlüssellochauhängung
Mounting dimension a	65,5 mm
Mounting dimension b	64 mm
Mounting dimension c	4,8 mm
Height	83 mm
Width	84 mm
Depth	124 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Derating from	40 °C

Conformity

Product standard	EN 61558-2-6, EN 62041 category I
EMC	EN 55011 B, EN 61000-3-2

Connection type 3

Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	metallic
No. of poles	1
PIN 1	PE
Connection	Screw terminals SK
Family construction form	terminal
Gender	female

Color contact carrier	green
No. of poles	3
PIN 1	+
PIN 2	-
PIN 3	-
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	5
PIN 1	+ 15 V
PIN 3	- 15 V
PIN 4	230 V
PIN 5	400 V