M12 DC/DC-TRANSFORMER

IN: 24 VDC - OUT: 10 VDC / 25 mA

Art.No.: 446139
Weight: 0.052 kg
Country of origin: CZ
Model designation: DEZENTRALE AUSGABEEINHEIT 24V/10V 20MA

Voltage regulator
12...30 V DC/ 10 V DC

[Link to Product]

Illustration







Product may differ from Image

Commercial data

URL Webshop	https://shop.murrelektronik.com/446139
GTIN	4048879025065
EU-Customs tariff number	85043121
US-Customs tariff number	8504312000
ECLASS-6.0	27049002

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-10

ECLASS-6.1	27210901
ECLASS-7.0	27210901
ECLASS-7.1	27210901
ECLASS-8.0	27210901
ECLASS-8.1	27210901
ECLASS-9.0	27210901
ECLASS-9.1	27210901
ECLASS-10.0.1	27210901
ECLASS-10.1	27210901
ECLASS-11.0	27210901
ECLASS-11.1	27210901
ECLASS-12.0	27210901
ECLASS-13.0	27210901
ECLASS-14.0	27210901
ETIM-5.0	EC002540
ETIM-6.0	EC002540
ETIM-7.0	EC002540
ETIM-8.0	EC002540
ETIM-9.0	EC002540
ETIM-10.0	EC002540
customs tariff number	85043121
EAN	4048879025065
Packaging unit	1
Electrical data | Input	
Input voltage DC	24 V
Input voltage DC min.	12 V
Input voltage DC max.	30 V
Input current	3 mA
Electrical data | Output	
Output voltage adjustable	No
Output voltage DC	10 V
Output current per channel max.	0,025 A
Installation | Connection	
Family construction form	M12
Device protection | Electrical	
Short-circuit protected	Yes
Mechanical data | Mounting data	
Height	24,5 mm
Width	24,5 mm
Depth	60,5 mm

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-10