

MSVD POWER SOCKET GB

to be discontinued - Last Time Order: 2023-03-31

Art.No.: 676316

Weight: 0.080 kg

Country of origin: CZ

Model designation: MSVD GB STECKDOSE SCHNAPP

England (white)

LED (yellow)

Screw terminals: max. 4 mm²**[Link to Product](#)****Commercial data**

URL Webshop	https://shop.murrelektronik.com/676316
GTIN	4048879039246
Customs tariff number	85366990
ECLASS-6.0	27189217
ECLASS-6.1	27142305
ECLASS-7.0	27142305
ECLASS-7.1	27142305
ECLASS-8.0	27142305
ECLASS-8.1	27142305
ECLASS-9.0	27142305
ECLASS-9.1	27142305
ECLASS-10.0.1	27142305
ECLASS-10.1	27142305
ECLASS-11.0	27142305
ECLASS-11.1	27142305
ECLASS-12.0	27142305
ECLASS-13.0	27142305
ECLASS-14.0	27142305
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879039246
Packaging unit	1

Electrical data | Supply

Operating voltage AC	250 V
Operating current	13 A

Installation

Connection cross section max.	4 mm ²
-------------------------------	-------------------

Installation | Connection

Connection	Screw terminals SK
------------	--------------------

Mechanical data | Mounting data

Height	75 mm
--------	-------

Width	70 mm
Depth	56 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail