MODLINK MSDD SOCKET INSERT IEC

250VAC/10A acc. EN 60320-2-2/F

Art.No.: 4000-68000-0080000
Weight: 0.026 kg
Country of origin: DE
Model designation: Fr.Modul-C14-250-10-SO

Appliance-outlet (IEC/EN 60320-2-2/F)
Spring clamp terminals: max. 2× 2.5 mm² (AWG 14)

Link to Product

Illustration

Product may differ from Image

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-0080000
GTIN	4048879038225
EU-Customs tariff number	85366990
US-Customs tariff number	8536694020
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC000020

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-14

ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
ETIM-9.0	EC000020
ETIM-10.0	EC000020
customs tariff number	85366990
EAN	4048879038225
Packaging unit	1
Mechanical data | Mounting data	
Height	88 mm
Width	51 mm
Depth	30 mm
Environmental characteristics | Climatic	
Ambient temperature (storage, transport)	-25 °C … 60 °C
Appliance-outlet	
Connection	plug-in connection
No. of poles	2 + PE
Connection geometry	6.3 x 0.8
Protection contact present	Yes
Operating voltage AC	250 V
Operating current	10 A
Current operating ULc	15 A

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-14