

MODLINK MSDD DATA INSERT

1×USB-A female/female

USB (form A – form A)
1× USB 3.0 (female/female) form A

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879037822
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	70,4 mm

Environmental characteristics | Climatic

Storage temperature min.	-10 °C
Storage temperature max.	60 °C

Shielding plate

Connection information	Threaded hole M4
------------------------	------------------

Tightening torque 0,9 Nm

USB	
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	1,5 A
USB specification	3.0
Data transmission rate max.	5000 MBit/s
Looking techniques	Snap-in connector