

MODLINK MSDD DATA INSERT

2×USB-A female/male 0,7m cable + 1×RJ45

- RJ45; USB; USB (A)
- 1 × RJ45, 8-pole metal, CAT5e (female/female)
- 2× USB (female/female/0.7 m cable) form A

Link to Product

Illustration



Product may differ from Image



| Commercial data                          |                  |
|------------------------------------------|------------------|
| ECLASS-6.0                               | 27189217         |
| ECLASS-6.1                               | 27189217         |
| ECLASS-7.0                               | 27189217         |
| ECLASS-8.0                               | 27189217         |
| ECLASS-9.0                               | 27189217         |
| ECLASS-10.1                              | 27182806         |
| ECLASS-11.1                              | 27182806         |
| ECLASS-12.0                              | 27182806         |
| ETIM-5.0                                 | EC002625         |
| customs tariff number                    | 85444290         |
| GTIN                                     | 4048879037761    |
| Packaging unit                           | 1                |
| Mechanical data   Mounting data          |                  |
| Height                                   | 88 mm            |
| Width                                    | 51 mm            |
| Depth                                    | 45 mm            |
| Environmental characteristics   Climatic |                  |
| Storage temperature min.                 | -30 °C           |
| Storage temperature max.                 | 60 °C            |
| Shielding plate                          |                  |
| Connection information                   | Threaded hole M4 |

Tightening torque 0,9 Nm

**USB**

|                                  |                   |
|----------------------------------|-------------------|
| Operating voltage AC             | 48 V              |
| Operating voltage DC             | 48 V              |
| Operating voltage DC (UL-listed) | 42,4 V            |
| Operating current max.           | 500 mA            |
| USB specification                | 2.0               |
| Data transmission rate max.      | 480 MBit/s        |
| Looking techniques               | Snap-in connector |

**RJ45**

|                                       |                   |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | RJ45              |
| Family type Back side                 | RJ45              |
| Cable category min.                   | Cat5e             |
| Looking techniques                    | Snap-in connector |