

MODLINK MSDD SOCKET INSERT INDIA

240VAC/5A

India (IS 1293)
with touch protection
Screw terminals

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879037297
Packaging unit	1
Mechanical data Mounting data	
Height	88 mm
Width	51 mm
Depth	21 mm
Environmental characteristics Climatic	
Storage temperature min.	-10 °C
Storage temperature max.	60 °C
India	
Connection cross section max.	1,5 mm²

AWG number max.	16
Operating voltage AC	240 V
Operating current	5 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes