MODLINK MSDD SINGLE COMBI INSERT USA NEMA 5-15

1xUSB-A female/female + 1xRJ45 female/female

Art.No.: 4000-68000-4030000
Weight: 0.053 kg
Country of origin: CZ
Model designation: Fr.Modul-AB-125-15-SO+RJ45+USB

1× NEMA 5-15 (plug-solder connection)
1× RJ45, 8-pole metal, CAT5e (female/female)
1× USB 3.0 (female/female) form A

Link to Product

Illustration

Product may differ from Image

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-4030000
GTIN	4048879037211
EU-Customs tariff number	85366990
US-Customs tariff number	8536694020
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-09

ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
ETIM-9.0	EC000020
ETIM-10.0	EC000020
customs tariff number	85366990
EAN	4048879037211
Packaging unit	1
Mechanical data | Mounting data	
Height	88 mm
Width	51 mm
Depth	58 mm
Environmental characteristics | Climatic	
Ambient temperature (storage, transport)	5 °C … 40 °C
USA	
Connection	Plug-solder connection
No. of poles	2 + PE
Protection contact present	Yes
Operating voltage AC	125 V
Operating current	15 A
USB	
USB specification	3.0
Looking techniques	Snap-in connector
Data transmission rate max.	5.000 Mbit/s
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	1,5 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
RJ45	
Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-09